







- 2. ALL MACHINING FLUIDS SHALL BE WATER SOLUBLE AND FREE OF SULFUR, CHLORINE AND SILICONE, SUCH AS CINCINNATI MILACRON'S CIMTECH 410 (STAINLESS STEEL)
- USING A VIBRATORY TOOL MARK PART AS INDICATED
 SCRIBE, ENGRAVE OR STAMP DRAWING PARTNUMBER ON NOTED SURFACE OF PART AND A THREE DIGIT SERIAL NUMBER. SERIAL NUMBERS START AT 001 FOR THE FIRST PART AND PROCEED CONSECUTIVELY.

USE .07" HIGH CHARACTERS. EXAMPLE: D020188- 001. A VIBRATORY TOOL MAY BE USED.









REV. DATE

24 JUNE 2004

21 APRIL 2002

А

DCN #

E040303-00

E0900107-v1

DRAWING TREE #

DIMENSIONS ARE IN INCHES		NAME	DATE	LIGO	CALIFORNIA INSTITUTE OF TE MASSACHUSETTS INSTITUTE C		
TOLERANCES:	DRAWN	CIT/RJ	05/02	Ligo	IGR, GLASGOW UNIVERSITY		
.XX ±0.01 .XXX ±0.005	CHECKED			SYSTEM	ADVANCED	LIGO	
ANGULAR±.25°				SUB-SYSTEN	⊿ SUS		
MATERIAL				NEXT ASSY	ROTATIONA	L ADJUS	TER
302, 304 OR 316 SSTL	COMMENTS	COMMENTS:			PART NAME ROTATIONAL ADJUSTER UPPER BLADE CLAMP LOWERSIDE ANGLED (2.5°)		
FINISH				SIZE DWG. N	D030464	REV.	
				SCALE: NTS		SHEET 1 OF 1	

FILE NAME/LOCATION: