

ACB Shelf length

3/4/2011

offset of top shelf, mm 140

offset of bottom shelf, mm 50

| Chamber | distance from COC HR to ACB back | | length of top shelf + extender | length of bottom shelf + extender | length of top shelf | length of bottom shelf | length of top extender |
|----------|-------------------------------------|-----|---|--|------------------------|------------------------------|------------------------------|
| | in | mm | mm | mm | mm | mm | mm |
| BSC1-H1 | 18.3 | 465 | 325 | 415 | 246 | 336 | 79 |
| BSC3-H1 | 23.7 | 602 | 462 | 552 | 246 | 336 | 216 |
| BSC9-H1 | 18.01 | 457 | 317 | 407 | 246 | 336 | 71 |
| BSC10-H1 | 18.05 | 458 | 318 | 408 | 246 | 336 | 72 |
| BSC1-L1 | 18.3 | 465 | 325 | 415 | 246 | 336 | 79 |
| BSC3-L1 | 23.7 | 602 | 462 | 552 | 246 | 336 | 216 |
| BSC4-L1 | 18.01 | 457 | 317 | 407 | 246 | 336 | 71 |
| BSC5-L1 | 18.05 | 458 | 318 | 408 | 246 | 336 | 72 |
| BSC5-H2 | 17 | 432 | 292 | 382 | 246 | 336 | 46 |
| BSC6-H2 | 17.01 | 432 | 292 | 382 | 246 | 336 | 46 |
| BSC7-H2 | 16.17 | 411 | 271 | 361 | 246 | 336 | 25 |
| BSC8-H2 | 17.07 | 434 | 294 | 384 | 246 | 336 | 48 |

| length of bottom extender |
|---------------------------------|
| mm |
| 79 |
| 216 |
| 71 |
| 72 |
| 79 |
| 216 |
| 71 |
| 72 |
| 46 |
| 46 |
| 25 |
| 48 |

