



H1 Handle, 1.25"

H2 Handle, 1.25"

Mouser  
534-9106

H3 Ferrule, 0.25"

H4 Ferrule, 0.25"

H5 Ferrule, 0.25"

H6 Ferrule, 0.25"

Mouser  
534-9121

M1 #6-32 1/4" flat

M2 #6-32 1/4" flat

M3 #6-32 1/4" flat

M4 #6-32 1/4" flat

M5 #6-32 1/4" flat

M6 #6-32 1/4" flat

McMaster-Carr  
91099A205

PN1  
Front Panel  
LIGO  
D1100754-v1

PN2  
Rear Panel  
LIGO  
D1100755-v1

PN3  
Top Panel  
LIGO  
D1100695-v1

E1 Standoff, 0.625"

E2 Standoff, 0.625"

Mouser  
534-1902F

PN4  
Bottom Panel  
LIGO  
D1100695-v1

H7 #4 screw, 3/8"

H8 #4 screw, 3/8"

Mouser  
534-9328

H9 #4 washer

H10 #4 washer

Mouser  
534-3358

PN5  
Side profile

PN6  
Side profile  
Frontpanel Express  
Side profile 1, 150mm

PN7  
Housing bracket  
Frontpanel Express  
Housing bracket 8 x per unit, natural anodized

PN8  
Assembly kit  
Frontpanel Express  
Assembly kit ISP/B3.0-NI DIN 7982, nickel-plated

PN9  
Screw kit  
Frontpanel Express  
Screw packet M3x6-965-NI DIN 965, nickel-plated

PN10  
D-Sub cable, DB9

PN11  
D-Sub cable, DB9

PN12  
D-Sub cable, DB9

PN13  
D-Sub cable, DB9

PN14  
IDC socket, 10pin

PN15  
IDC socket, 10pin

PN16  
IDC socket, 10pin

PN17  
IDC socket, 10pin

PN18  
Screwlock kit

|   |  |              |                      |
|---|--|--------------|----------------------|
| Title<br><b>Controls Concentrator ASC Demodulator</b> |  |              |                      |
| Size<br>A   | Number<br><b>D1100696</b>                                    |              | Revision<br><b>1</b> |
| Date:   | 10/4/2011  | Sheet 1 of 1 |                      |
| File:   | C:\Users\...\ConcentratorDemodASC1.Sch Drawn By: Daniel Sigg |              |                      |